


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/19/20	PHOSPODAR

WIRING MAP

LC	COLOR	1X24	REF DES
1	BLUE	1	J1
2	ORANGE	2	
3	GREEN	3	
4	BROWN	4	
5	GRAY	5	
6	WHITE	6	
7	RED	7	
8	BLACK	8	
9	YELLOW	9	
10	PURPLE	10	
11	ROSE	11	
12	AQUA	12	
13	BLUE/BLACK	13	
14	ORANGE/BLACK	14	
15	GREEN/BLACK	15	
16	BROWN/BLACK	16	
17	GRAY/BLACK	17	
18	WHITE/BLACK	18	
19	RED/BLACK	19	
20	BLACK / WHITE	20	
21	YELLOW/BLACK	21	
22	PURPLE/BLACK	22	
23	ROSE/BLACK	23	
24	AQUA/BLACK	24	



PART NUMBER	METERS (FEET)
MPF24OM3-09LCR-1	1.0 (3.28)
MPF24OM3-09LCR-3	3.0 (9.84)
MPF24OM3-09LCR-5	5.0 (16.40)
MPF24OM3-09LCR-10	10.0 (32.81)

- NOTES:
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY PHOSPODAR APPROVED BY PHOSPODAR	DATE 11/19/2020 11/19/2020 11/19/2020	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY FIBER OPTICS
SIZE A		CAGE CODE 43321	ITEM NO. MPF24OM3-09LCR	REV. A
SCALE: NONE		CAD FILE: MPF24OM3-09LCR.SLDDRW		SHEET 1 OF 1