


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/30/2021	PHOSPODAR

WIRING MAP

J1	COLOR	J2	J3
1	BLUE	1	
2	ORANGE	2	
3	GREEN	3	
4	BROWN	4	
5	GRAY	5	
6	WHITE	6	
7	RED	7	
8	BLACK	8	
9	YELLOW	9	
10	PURPLE	10	
11	ROSE	11	
12	AQUA	12	
13	BLUE w/TRACER		1
14	ORANGE w/TRACER		2
15	GREEN w/TRACER		3
16	BROWN w/TRACER		4
17	GRAY w/TRACER		5
18	WHITE w/TRACER		6
19	RED w/TRACER		7
20	BLACK w/TRACER		8
21	YELLOW w/TRACER		9
22	PURPLE w/TRACER		10
23	ROSE w/TRACER		11
24	AQUA w/TRACER		12



PART NUMBER	METERS (FEET)
MPM24212SMZ-1	1.0 (3.28)
MPM24212SMZ-3	3.0 (9.84)
MPM24212SMZ-5	5.0 (16.40)
MPM24212SMZ-10	10.0 (32.81)

NOTES:

1. MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC
2. ALL CONNECTORS INCLUDE A DUST CAP (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 03/30/2021 03/30/2021 03/30/2021	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION FIBER AG CONV HARNESS, MPO24 (M) TO 2XMPO12 (M)	
THIRD-ANGLE PROJECTION 	SIZE A CAGE CODE 43321 ITEM NO. MPM24212SMZ	SCALE: NONE CAD FILE: MPM24212SMZ.SLDDRW	REV. A SHEET 1 OF 1