


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/24/21	PHOSPODAR



WIRING MAP

J1	J2	J3	COLOR	J4	J5
		12	BLUE		1
		11	ORANGE		2
		10	GREEN		3
		9	BROWN		4
	12		GRAY		5
	11		WHITE		6
	10		RED		7
	9		BLACK		8
12			YELLOW		9
11			PURPLE		10
10			ROSE		11
9			AQUA		12
	4		BLUE w/TRACER		1
	3		ORANGE w/TRACER		2
	2		GREEN w/TRACER		3
	1		BROWN w/TRACER		4
	4		GRAY w/TRACER		5
	3		WHITE w/TRACER		6
	2		RED w/TRACER		7
	1		BLACK w/TRACER		8
4			YELLOW w/TRACER		9
3			PURPLE w/TRACER		10
2			ROSE w/TRACER		11
1			AQUA w/TRACER		12



PART NUMBER	LENGTH METERS (FEET)	BREAKOUT METERS (FEET)
MPM308212SMZ-1	1.0 (3.28)	0.3 (1.00)
MPM308212SMZ-3	3.0 (9.84)	0.6 (2.00)
MPM308212SMZ-5	5.0 (16.40)	
MPM308212SMZ-10	10.0 (32.81)	

- NOTES:
- MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC.
 - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 - PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DZINN	03/24/2021		CATEGORY FIBER OPTICS PRODUCT DESCRIPTION FIBER CONV HARNESS, 3XMPO8 (M) TO 2XMPO12 (M)
	CHECKED BY DFRISIELLO	03/24/21		
	APPROVED BY PHOSPODAR	03/24/21		
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A CAGE CODE 43321 ITEM NO. MPM308212SMZ	