


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/11/22	PHOSPODAR

**WIRING MAP  
TYPE B**

J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	GREEN	10
4	BROWN	9
5	GRAY	8
6	WHITE	7
7	RED	6
8	BLACK	5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1
13	BLUE/BLACK	24
14	ORANGE/BLACK	23
15	GREEN/BLACK	22
16	BROWN/BLACK	21
17	GRAY/BLACK	20
18	WHITE/BLACK	19
19	RED/BLACK	18
20	BLACK/WHITE	17
21	YELLOW/BLACK	16
22	PURPLE/BLACK	15
23	ROSE/BLACK	14
24	AQUA/BLACK	13



PART NUMBER	METERS [FEET]
MPMF24OM4BZ-1	1.0 [3.28]
MPMF24OM4BZ-3	3.0 [9.84]
MPMF24OM4BZ-5	5.0 [16.40]
MPMF24OM4BZ-10	10.0 [32.81]

**NOTES:**

1. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
2. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:  <math>\leq 12</math> [305] = <math>+1</math> [25] / -0  <math>&gt; 12</math> [305] <math>\leq 60</math> [1524] = <math>+2</math> [51] / -0  <math>&gt; 60</math> [1524] <math>\leq 120</math> [3048] = <math>+4</math> [102] / -0  <math>&gt; 120</math> [3048] <math>\leq 300</math> [7620] = <math>+6</math> [152] / -0  <math>&gt; 300</math> [7620] = <math>+5\%</math> / -0         </p> <p>ALL OTHER DIMENSIONAL TOLERANCES:  <math>.X = \pm .2</math> [5]      FRACTIONS  <math>.XX = \pm .02</math> [5]      <math>\pm 1/32</math>  <math>.XXX = \pm .005</math> [1.3]      ANGLES <math>\pm 1^\circ</math> </p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p><b>L-COM</b> an INFINIT<sup>®</sup> brand</p> <p>CATEGORY</p> <p>FIBER OPTICS</p>
	DRAWN BY DMAY	02/22/2022	
	CHECKED BY JJOHNSTON	3/11/22	
<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>		<p>PRODUCT DESCRIPTION  <b>MPO W/ PINS TO MPO NO PINS, 24 FIBER, TYPE B 40GB 50/125 OM4 MMF, LSZH JACKET</b> </p>	
<p>COLOR VARIATIONS MAY OCCUR</p>		SIZE <b>A</b>	CAGE CODE <b>43321</b>
<p>SCALE: NONE</p>		ITEM NO. <b>MPMF24OM4BZ</b>	REV. <b>A</b>
<p>CAD FILE: MPMF24OM4BZ.SLDDRW</p>		<p>SHEET 1 OF 1</p>	