


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/11/22	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPMF8OM4AR-1	1.0 [3.28]
MPMF8OM4AR-3	3.0 [9.84]
MPMF8OM4AR-5	5.0 [16.40]
MPMF8OM4AR-10	10.0 [32.81]

NOTES:

1. ALL CONNECTORS ACCCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
2. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm].
OVERALL CABLE LENGTH TOLERANCE:
≤12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:

.X = ± .2 [5] .XX = ± .02 [5] .XXX = ± .005 [1.3]

FRACTIONS
± 1/32
ANGLES ± 1°



APPROVALS

DRAWN BY

DMAY

2/24/22

CHECKED BY

JJOHNSTON

3/11/22

APPROVED BY

PHOSPODAR

3/11/22

DATE

2/24/22

3/11/22

3/11/22



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

FIBER OPTICS

PRODUCT DESCRIPTION

MPO W/ PINS TO MPO NO PINS, 8 FIBER, TYPE A,
40GB 50/125 OM4 MMF, OFNR JACKET

SIZE

A

43321

MPMF8OM4AR

REV.

A

SCALE: NONE

CAD FILE: MPMF8OM4AR.SLDDRW

SHEET 1 OF 1