


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 3/11/22 | PHOSPODAR |
| | | | |
| | | | |



| WIRING MAP TYPE B | | |
|-------------------|--------------|----|
| J1 | COLOR | J2 |
| 1 | BLUE | 12 |
| 2 | ORANGE | 11 |
| 3 | GREEN | 10 |
| 4 | BROWN | 9 |
| 5 | GRAY | 8 |
| 6 | WHITE | 7 |
| 7 | RED | 6 |
| 8 | BLACK | 5 |
| 9 | YELLOW | 4 |
| 10 | PURPLE | 3 |
| 11 | ROSE | 2 |
| 12 | AQUA | 1 |
| 13 | BLUE/BLACK | 24 |
| 14 | ORANGE/BLACK | 23 |
| 15 | GREEN/BLACK | 22 |
| 16 | BROWN/BLACK | 21 |
| 17 | GRAY/BLACK | 20 |
| 18 | WHITE/BLACK | 19 |
| 19 | RED/BLACK | 18 |
| 20 | BLACK/WHITE | 17 |
| 21 | YELLOW/BLACK | 16 |
| 22 | PURPLE/BLACK | 15 |
| 23 | ROSE/BLACK | 14 |
| 24 | AQUA/BLACK | 13 |



| PART NUMBER | METERS [FEET] |
|----------------|---------------|
| MPMM24OM4BZ-1 | 1.0 [3.28] |
| MPMM24OM4BZ-3 | 3.0 [9.84] |
| MPMM24OM4BZ-5 | 5.0 [16.40] |
| MPMM24OM4BZ-10 | 10.0 [32.81] |

- NOTES:
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 - PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | | |
|---|--|---|---|---------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| | DRAWN BY DMAY | 02/22/2022 | | CATEGORY FIBER OPTICS |
| | CHECKED BY JJOHNSTON | 3/11/22 | | |
| | APPROVED BY PHOSPODAR | 3/11/22 | | |
| THIRD-ANGLE PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION MPO W/ PINS TO MPO W/ PINS, 24 FIBER, TYPE B 40GB 50/125 OM4 MMF, LSZH JACKET | SCALE: NONE CAD FILE: MPMM24OM4BZ.SLDDRW SHEET 1 OF 1 | |
| COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 | ITEM NO. MPMM24OM4BZ | REV. A |