


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/19/2021	GUTTADAURO



**NOTES:**

- VOLTAGE RATING:**  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec  
CONDUCTOR RESISTANCE ≤ 8.88Ω/1000M  
VOLTAGE RATING AC 300V
- CABLE MARKING :**  
(UL) E135710-F5 SJT 3×14AWG 105°C 300V VW-1  
c(UL) SJT 3×2.08 mm<sup>2</sup> (14AWG) 105°C 300V FT2
- OPTIONAL LABELS:**  
OPTIONAL LABEL(S) MAY INCLUDE  
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.**
- ALL DIMENSIONS FOR REFERENCE ONLY.**

ITEM NUMBER	LENGTH INCHES [MM]
N515P-C13R-15-03F	36.0 ± 0.4 [915 ± 10.0]
N515P-C13R-15-06F	72.0 ± 0.8 [1830 ± 20.0]
N515P-C13R-15-10F	120.0 ± 1.2 [3050 ± 30.0]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY: MVEERAPPAN CHECKED BY: DFRISIELLO APPROVED BY: GUTTADAURO	DATE 10/19/2021 10/19/2021 10/19/2021	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>POWER PRODUCTS</b>
SIZE <b>A</b>		CAGE CODE <b>43321</b>	ITEM NO. <b>N515P-C13R-15</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: N515P-C13R-15.SLDDRW		SHEET 1 OF 1