



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/19/2021	GUTTADAURO



ITEM NUMBER	LENGTH INCHES [MM]
N520P-N520R-20-03F	36.0 ± 0.4 [910 ± 10.0]
N520P-N520R-20-06F	72.0 ± 0.8 [1830 ± 20.0]
N520P-N520R-20-10F	120.0 ± 1.2 [3050 ± 30.0]

**NOTES:**

- VOLTAGE RATING:  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec  
CONDUCTOR RESISTANCE  $\leq 3.51\Omega/1000M$   
VOLTAGE RATING AC 300V
- CABLE MARKING :  
(UL) E135710-F5 SJTOW 3X10AWG 105°C 300V VW-1 WATER RESISTANT  
c(UL) SJTOW 3X5.26mm2(10AWG) 105°C 300V FT2
- OPTIONAL LABELS:  
OPTIONAL LABEL(S) MAY INCLUDE  
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.
- ALL DIMENSIONS FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY MVEERAPPAN	10/19/2021	
THIRD-ANGLE PROJECTION 	APPROVED BY GUTTADAURO	10/19/2021	CATEGORY <b>POWER PRODUCTS</b>
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>
PRODUCT DESCRIPTION <b>N5-20P - N5-20R Power Cord, 20A, 125V</b>		ITEM NO. <b>N520P-N520R-20</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: N520P-N520R-20.SLDDRW	SHEET 1 OF 1