


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/30/2023	BPUCHASKI	GUTTADAURO



NOTES:

1. REFERENCE: VOLTAGE RATING 20A/125V
2. APPROVALS: UL APPROVED
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</div> <div>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 &gt;12 [305] ≤60 [1524] = +2 [51] / -0 &gt;60 [1524] ≤120 [3048] = +4 [102] / -0 &gt;120 [3048] ≤300 [7620] = +6 [152] / -0 &gt;300 [7620] = +5% / -0</div> <div>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]</div> <div>THIRD-ANGLE PROJECTION </div>	APPROVALS	DATE	<div><div>an INFINITI® brand</div></div> <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>			
	DRAWN BY BPUCHASKI	05/30/2023				
	CHECKED BY DGUST	05/30/2023	CATEGORY	POWER CORD		
	APPROVED BY GUTTADAURO	05/30/2023				
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION N5-20P/C19, Industrial STJOW Cord, 125V, 20A			
COLOR VARIATIONS MAY OCCUR			SIZE A	CAGE CODE 43321	ITEM NO. OWN520C19-20	REV. A
			SCALE: NONE   CAD FILE: OWN520C19-20.SLDDRW			SHEET 1 OF 1