


| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
|------|-----|-----------------|------------|------------|----------|
| | A | INITIAL RELEASE | 05/01/2025 | AKRESOWSKI | DGUST |



NOTES:

1. DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 SEC.
2. CONDUCTOR RESISTANCE: 5.69Ω/1000M AT 20°C.
3. CABLE VOLTAGE RATING: AC 300V AT 20°C.
4. CABLE ASSEMBLY RATED FOR 125V/15A.
5. CABLE MARKING : (ETL) US 3176559 SJTOW 3X12AWG 105°C -50°C 300V VW-1 C(ETL) SJTOW 3X3.31mm² (12AWG) FT2 / (ETL) US 5019033 SJTOW 3X12AWG 105°C -50°C 300V VW-1 C(ETL) SJTOW 3X3.31mm² (12AWG) FT2.
6. RED NEON LAMP WARNING:
BLACK - RESISTANCE PIN
WHITE - NO RESISTANCE PIN.
7. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
8. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
9. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| ITEM NO | LENGTH | |
|----------------------|--------|------|
| | METERS | FEET |
| PCI032LEDSJTOW-50FT | 15.24 | 50 |
| PCI032LEDSJTOW-100FT | 30.48 | 100 |

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm 0.2 [5]$ FRACTIONS
 $XX = \pm 0.02 [0.5]$ $\pm 1/32$
 $XXX = \pm .005 [0.13]$ ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 $\leq 12 [305] = +1 [25] / -0$
 $> 12 [305] \leq 60 [1524] = +2 [51] / -0$
 $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$
 $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$
 $> 300 [7620] = +5\% / -0$

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

| | |
|-------|--------|
| SCALE | Sheet |
| NONE | 1 OF 1 |

DESCRIPTION
POWER CABLE ASSY, NEMA 5-15P TO NEMA 5-15R LED POWER
INDICATOR, SJTOW 12AWG X 3C 105°C

| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | REV |
|------|-----------|------------|----------------|-----|
| A | 43321 | AKRESOWSKI | PCI032LEDSJTOW | A |