





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/03/2021	MBLACKWOOD



PART NUMBER	LENGTH FEET	LENGTH METERS
PPA00002RD-01F	1.0	.30
PPA00002RD-02F	2.0	.61
PPA00002RD-03F	3.0	.91
PPA00002RD-06F	6.0	1.83
PPA00002RD-08F	8.0	2.44
PPA00002RD-15F	15.0	4.57

NOTES:

- VOLTAGE RATING: AC \geq 1500V/S
- CONNECTOR C13 POWER RATING: 15A UL-E257089
- CONNECTOR C14 POWER RATING: 15A UL-E257089
- CABLE: SJT 14AWGx3, 300V, 60°C VW-1 E313867 FT1
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.
- ALL DIMENSIONS FOR REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY BPUCHASKI	DATE 02/03/2021	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY DZINN	02/03/2021		CATEGORY POWER PRODUCT
THIRD-ANGLE PROJECTION 	APPROVED BY MBLACKWOOD	02/03/2021	PRODUCT DESCRIPTION Heavy Duty CPU/PDU Power Cord - C14 to C13 - 15Amp	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. PPA00002RD
SCALE: NONE		CAD FILE: PPA00002RD.SLDDRW		SHEET 1 OF 1