



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/23/12	D.GRIFFIN



- NOTES:
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
 2. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS D. DESJARDIN CHECKED BY D. FRISIELLO APPROVED BY D. PARHAM	DATE 8/16/12 8/20/12 8/20/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY DATA
PROJECTION 	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION INTERFACE MODULE, DB15 FEMALE	SIZE A FSCM NO. 43321 DWG. NO. RBMIDB15F REV. A
SCALE: NONE CAD FILE: RBMIDB15F.SLDDRW SHEET 1 OF 1			