








THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

CODING	JACK	COLOR
103		BLACK
104		WHITE
105		BLUE
106		BORDEAUX
107		VIOLET
108		CURRY
109		WATER BLUE

NOTES:

ELECTRICAL DATA:

1. IMPEDANCE: 50Ω
2. FREQUENCY RANGE: DC TO 3GHz
3. VSWR: 1.35:1


MECHANICAL:

1. BODY: PLASTIC
2. CONTACT: BRASS, GOLD PLATED
3. INSULATION: PTFE





ALL DIMENSIONS FOR REFERENCE ONLY.


REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



CODING 108 SHOWN

RECOMMENDED
MTG HOLE PATTERN

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-comTM an INFINIT[®] brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY SREITER		03/15/2023		CATEGORY		PCB CONNECTOR	
		CHECKED BY DWANG		03/30/2023					
		APPROVED BY AGANWANI		03/30/2023					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION		FAKRA PLUG RIGHT ANGLE CONNECTOR SOLDER ATTACHMENT THRU HOLE PCB, BORDEAUX COLOR			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. RFPCB-FAKRA-MR-4G106		REV A	
				SCALE: NONE	CAD FILE: RFPCB-FAKRA-MR-4G106.SLDDRW			SHEET 1 OF	