L-com Specification/Procedure

RG6

Revison: G

Revision Date: 10/22/14

Revised By: S.Li

Bulk Cable Specification

RG6/U Coaxial Cable

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
RG6-100	COIL	LOGO BAG	100 FT.
RG6-500	SPOOL	STRETCH WRAP	500 FT.
RG6-1K	SPOOL	STRETCH WRAP	1000 FT.



NOMINAL IMPEDANCE:

75 OHMS

CONDUCTOR MATERIAL AND DIAMETER

18 AWG. SOLID BARE Ø.040" NOMINAL

SHIELDING TYPE AND COVERAGE

1ST LAYER; DUOFOIL 100% COVERAGE 2ND LAYER; TINNED COPPER BRAID 60% COVERAGE

INSULATION MATERIAL AND DIAMETER

GAS INJECTED FOAM POLYETYLENE Ø.180" NOMINAL

JACKET MATERIAL AND DIAMETER

BLACK PVC; Ø.270 NOMINAL

OPERATING TEMPERATURE:

-10°C - +70°C MIN

NOTE:

SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC