


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	01/19/01	MCCORMICK
B	REVISED TABLE ECN 1128	06/10/02	MCCORMICK
C	REVISED CABLE MARKERS (ECN 1274)	01/03/03	MCCORMICK



PART NUMBER	LENGTH	
	METERS	FEET
SFODST-FC-01	1.0	3.3
SFODST-FC-02	2.0	6.6
SFODST-FC-03	3.0	9.8
SFODST-FC-04	4.0	13.1
SFODST-FC-05	5.0	16.4

- NOTES:  
 1. CONNECTOR ASSEMBLY USES PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 .X ±.1  
 .XX ±.05  
 .XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/03/01
CHECKED BY DFP	01/19/01
APPROVED BY R.CARRICK	01/19/01

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

**L-com**  
 CONNECTIVITY PRODUCTS  
 45 BEECHWOOD DRIVE  
 NORTH ANDOVER, MA 01845

PRODUCT DESCRIPTION  
**9/125 SINGLEMODE FIBER**

DRAWING TITLE  
**OUTLINE DRAWING**

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>SFODST-FC-01-OD1</b>	REV. <b>C</b>
SCALE: 1:2		CAD FILE: SFODST-FC-01-OD1.SLDDRW	SHEET 1 OF 1