


Bulk Cable Specification

<p>Cross-Sectional View</p> 		<p>Color Code</p> <ol style="list-style-type: none"> 1. Black 2. Brown 3. Red 4. Orange 5. Yellow 6. Green 7. Blue 8. Purple 9. Gray 10. White
ITEM		DESCRIPTION
Conductor	No. of Conductors	10
	Material	Bare Copper
	Construction	26 AWG Stranded (7/0.16±0.008MM)
Insulation	Material	Polypropylene
	Nominal Diameter	0.037" [0.95MM]
	Thickness	0.007" [0.18MM] Minimum
Shielding	Material	N/A
	Coverage	N/A
Drain Wire	Material	N/A
	Construction	N/A
Braiding	Material	N/A
	Coverage	N/A
Jacket	Material	PVC
	Thickness	0.020" [0.51MM] Minimum
	Nominal Diameter	Oval(0.098"[2.50MM]*0.433[11.0MM])
	Color	Black
ELECTRICAL PROPERTIES		
Conductor Resistance	150Ω/KM MAX,26AWG@20°C	
Insulation Resistance	N/A	
Impedance	N/A	
Maximum Voltage	150V	
Maximum Current Rating	N/A	
LISTINGS / RATINGS		
RoHS Compliant	Yes	
UL Style	20251	
MISCELLANEOUS		
Operating Temperature Range	-10°C ~+80°C	
Storage Temperature Range	-10°C ~+60°C	
Minimum Bending Radius	N/A	
Packaging	1000 FT: Spool with Stretch Wrap	