


Cross-Sectional View 		Color Code 1. Black 2. Red 3. Green 4. Yellow
ITEM		DESCRIPTION
Conductor	No. of Conductors	4
	Material	Bare Copper
	Construction	26 AWG Stranded (7x34)
Insulation	Material	Polypropylene
	Nominal Diameter	0.038" [0.97mm]
	Thickness	0.005" [0.13mm] Minimum
Shielding	Material	N/A
	Coverage	N/A
Drain Wire	Material	N/A
	Construction	N/A
Braiding	Material	N/A
	Coverage	N/A
Jacket	Material	PVC
	Thickness	0.016" [0.41mm] Minimum
	Nominal Diameter	Oval
	Color	Silver Satin
ELECTRICAL PROPERTIES		
Conductor Resistance		N/A
Insulation Resistance		N/A
Impedance		N/A
Maximum Voltage		150V
Maximum Current Rating		N/A
LISTINGS / RATINGS		
RoHS Compliant		Yes
Flammability Rating		VW-1
UL Style		20251
MISCELLANEOUS		
Operating Temperature		+60°C Maximum
Minimum Bending Radius		N/A
Packaging	100 FT: Coil with Stretch Wrap in accordance with L-com specification PS-0031 500 FT: Reel with Stretch Wrap 1000 FT: Reel with Stretch Wrap	