




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/12	D.FRISIELLO
B	ECN6202: CHANGED BOOTS FROM "LSZH" TO "PE". CHNGD TO SHIELDED PLUG	6/11/12	D.DESJARDIN
C	ECN6553: UPDATED NOTES. CHANGED PE NOTE TO LSZH	1/14/13	D.DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	12/1/14	D.FRISIELLO



**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS D.FRISIELLO CHECKED BY J.RUST APPROVED BY D. GALLAGHER	DATE 2/3/12 2/3/12 2/3/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
		DWG. NO. <b>TRD815SZRA10</b>	REV. <b>D</b>
		SCALE: NONE	CAD FILE: TRD815SZRA10.SLDDRW
		SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SZRA10BLK-1	BLACK	1.0 [0.30]	TRD815SZRA10RD-1	RED	1.0 [0.30]	TRD815SZRA10GRY-1	GRAY	1.0 [0.30]
TRD815SZRA10BLK-2	BLACK	2.0 [0.61]	TRD815SZRA10RD-2	RED	2.0 [0.61]	TRD815SZRA10GRY-2	GRAY	2.0 [0.61]
TRD815SZRA10BLK-3	BLACK	3.0 [0.91]	TRD815SZRA10RD-3	RED	3.0 [0.91]	TRD815SZRA10GRY-3	GRAY	3.0 [0.91]
TRD815SZRA10BLK-5	BLACK	5.0 [1.52]	TRD815SZRA10RD-5	RED	5.0 [1.52]	TRD815SZRA10GRY-5	GRAY	5.0 [1.52]
TRD815SZRA10BLK-7	BLACK	7.0 [2.13]	TRD815SZRA10RD-7	RED	7.0 [2.13]	TRD815SZRA10GRY-7	GRAY	7.0 [2.13]
TRD815SZRA10BLK-10	BLACK	10.0 [3.05]	TRD815SZRA10RD-10	RED	10.0 [3.05]	TRD815SZRA10GRY-10	GRAY	10.0 [3.05]
TRD815SZRA10BLK-15	BLACK	15.0 [4.57]	TRD815SZRA10RD-15	RED	15.0 [4.57]	TRD815SZRA10GRY-15	GRAY	15.0 [4.57]
TRD815SZRA10BLK-20	BLACK	20.0 [6.10]	TRD815SZRA10RD-20	RED	20.0 [6.10]	TRD815SZRA10GRY-20	GRAY	20.0 [6.10]
TRD815SZRA10BLK-25	BLACK	25.0 [7.62]	TRD815SZRA10RD-25	RED	25.0 [7.62]	TRD815SZRA10GRY-25	GRAY	25.0 [7.62]
TRD815SZRA10BLK-30	BLACK	30.0 [9.14]	TRD815SZRA10RD-30	RED	30.0 [9.14]	TRD815SZRA10GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C5E LSZ FTP RGT-DWN			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRD815SZRA10	REV. <b>D</b>
SCALE: NONE		CAD FILE: TRD815SZRA10.SLDDRW	SHEET 2 OF 2