



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/8/12	D.FRISIELLO
B	ECN 6202: CHANGED BOOTS FROM "LSZH" TO "PE"	6/8/12	D.DESJARDIN
C	ECN6551: UPDATED NOTES. CHANGED PE NOTE TO LSZH	12/28/12	D.DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/21/14	D.FRISIELLO



WIRING MAP



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	1/31/12		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY J.RUST	1/31/12	PRODUCT DESCRIPTION C5E LSZ UTP RGT-RGT	
	APPROVED BY D. GALLAGHER	1/31/12	SIZE A	FSCM NO. 43321
PROJECTION 	COLOR VARIATIONS MAY OCCUR		DWG. NO. TRD815ZRA14	REV. D
SCALE: NONE			CAD FILE: TRD815ZRA14.SLDDRW	
			SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA14BLK-1	BLACK	1.0 [0.30]	TRD815ZRA14RD-1	RED	1.0 [0.30]	TRD815ZRA14GRY-1	GRAY	1.0 [0.30]
TRD815ZRA14BLK-2	BLACK	2.0 [0.61]	TRD815ZRA14RD-2	RED	2.0 [0.61]	TRD815ZRA14GRY-2	GRAY	2.0 [0.61]
TRD815ZRA14BLK-3	BLACK	3.0 [0.91]	TRD815ZRA14RD-3	RED	3.0 [0.91]	TRD815ZRA14GRY-3	GRAY	3.0 [0.91]
TRD815ZRA14BLK-5	BLACK	5.0 [1.52]	TRD815ZRA14RD-5	RED	5.0 [1.52]	TRD815ZRA14GRY-5	GRAY	5.0 [1.52]
TRD815ZRA14BLK-7	BLACK	7.0 [2.13]	TRD815ZRA14RD-7	RED	7.0 [2.13]	TRD815ZRA14GRY-7	GRAY	7.0 [2.13]
TRD815ZRA14BLK-10	BLACK	10.0 [3.05]	TRD815ZRA14RD-10	RED	10.0 [3.05]	TRD815ZRA14GRY-10	GRAY	10.0 [3.05]
TRD815ZRA14BLK-15	BLACK	15.0 [4.57]	TRD815ZRA14RD-15	RED	15.0 [4.57]	TRD815ZRA14GRY-15	GRAY	15.0 [4.57]
TRD815ZRA14BLK-20	BLACK	20.0 [6.10]	TRD815ZRA14RD-20	RED	20.0 [6.10]	TRD815ZRA14GRY-20	GRAY	20.0 [6.10]
TRD815ZRA14BLK-25	BLACK	25.0 [7.62]	TRD815ZRA14RD-25	RED	25.0 [7.62]	TRD815ZRA14GRY-25	GRAY	25.0 [7.62]
TRD815ZRA14BLK-30	BLACK	30.0 [9.14]	TRD815ZRA14RD-30	RED	30.0 [9.14]	TRD815ZRA14GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY: TELECOM/MODULAR			
PRODUCT DESCRIPTION: C5E LSZ UTP RGT-RGT			
SIZE: A	FSCM NO.: 43321	DWG. NO.: TRD815ZRA14	REV.: D
SCALE: NONE		CAD FILE: TRD815ZRA14.SLDDRW	
			SHEET 2 OF 2