


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/20/14	D.FRISIELLO



P1
RJ45 MODULAR
UNSHIELDED PLUG
GOLD PLATED CONTACTS
(8P8C)

P2
RJ45 MODULAR
UNSHIELDED PLUG
GOLD PLATED CONTACTS
(8P8C)

WIRING MAP



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS D.FRISIELLO CHECKED BY J.RUST APPROVED BY D.GALLAGHER	DATE 1/26/12 1/26/12 1/26/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR PRODUCT DESCRIPTION C5E LSZH UTP STR-UP	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRD815ZRA2	REV. E
SCALE: NONE		CAD FILE: TRD815ZRA2.SLDDRW		SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA2BLK-1	BLACK	1.0 [0.30]	TRD815ZRA2RD-1	RED	1.0 [0.30]	TRD815ZRA2GRY-1	GRAY	1.0 [0.30]
TRD815ZRA2BLK-2	BLACK	2.0 [0.61]	TRD815ZRA2RD-2	RED	2.0 [0.61]	TRD815ZRA2GRY-2	GRAY	2.0 [0.61]
TRD815ZRA2BLK-3	BLACK	3.0 [0.91]	TRD815ZRA2RD-3	RED	3.0 [0.91]	TRD815ZRA2GRY-3	GRAY	3.0 [0.91]
TRD815ZRA2BLK-5	BLACK	5.0 [1.52]	TRD815ZRA2RD-5	RED	5.0 [1.52]	TRD815ZRA2GRY-5	GRAY	5.0 [1.52]
TRD815ZRA2BLK-7	BLACK	7.0 [2.13]	TRD815ZRA2RD-7	RED	7.0 [2.13]	TRD815ZRA2GRY-7	GRAY	7.0 [2.13]
TRD815ZRA2BLK-10	BLACK	10.0 [3.05]	TRD815ZRA2RD-10	RED	10.0 [3.05]	TRD815ZRA2GRY-10	GRAY	10.0 [3.05]
TRD815ZRA2BLK-15	BLACK	15.0 [4.57]	TRD815ZRA2RD-15	RED	15.0 [4.57]	TRD815ZRA2GRY-15	GRAY	15.0 [4.57]
TRD815ZRA2BLK-20	BLACK	20.0 [6.10]	TRD815ZRA2RD-20	RED	20.0 [6.10]	TRD815ZRA2GRY-20	GRAY	20.0 [6.10]
TRD815ZRA2BLK-25	BLACK	25.0 [7.62]	TRD815ZRA2RD-25	RED	25.0 [7.62]	TRD815ZRA2GRY-25	GRAY	25.0 [7.62]
TRD815ZRA2BLK-30	BLACK	30.0 [9.14]	TRD815ZRA2RD-30	RED	30.0 [9.14]	TRD815ZRA2GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C5E LSZ UTP STR-UP			
SIZE A	FSCM NO. 43321	DWG. NO. TRD815ZRA2	REV. E
SCALE: NONE		CAD FILE: TRD815ZRA2.SLDDRW	SHEET 2 OF 2