





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/06/18	JLABOY



PART NUMBER	LENGTH METERS [FEET]
U3A00028-03M	0.3 [.98]
U3A00028-05M	0.5 [1.64]
U3A00028-075M	0.75 [2.46]
U3A00028-1M	1.0 [3.28]
U3A00028-105M	1.5 [4.92]



CABLE:
 UL STYLE 21551, 2X, TWISTED PAIR, 30AWG WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE. ONE UNSHIELDED TWISTED PAIR, 30AWG. 2 COND., 24AWG. OVERALL BRAID SHIELD, 65%
 JACKET: LSZH, BLACK
 (NOM DIA. .217"[5.5], TEMPERATURE RANGE:-10~+80 °C)

NOTES:
 1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 2. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS	DATE
	DRAWN BY S.LI	06/27/17
	CHECKED BY B.ZHANG	06/27/17
	APPROVED BY S.PAN	06/27/17
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR

L-com Global Connectivity
 50 HIGH STREET
 NORTH ANDOVER, MA
 01845

CATEGORY: **USB**

PRODUCT DESCRIPTION: **CA,USB3.0 A/A LATCH LSZH**

SIZE A	FSCM NO. 43321	DWG. NO. U3A00028	REV. A
------------------	--------------------------	-----------------------------	------------------

SCALE: NONE | CAD FILE: U3A00028.SLDDRW | SHEET 1 OF 1