


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/11/2023	GUTTADAURO





PART NUMBER	LENGTH (MILLIMETER)
USB2.0-RS232-1M	1000
USB2.0-RS232-1.5M	1500
USB2.0-RS232-2M	2000

FEATURES:

- USB 2.0 VERSION
- OVER 1Mbps DATA TRANSFER RATE.
- COMPATIBLE WITH WINDOWS, MAC, LINUX, ANDROID SYSTEM

PACKAGING:

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS SLI	DATE 04/18/2023	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY GUTTADAURO	DATE 04/18/2023	
APPROVED BY GUTTADAURO	DATE 04/18/2023	PRODUCT DESCRIPTION USB TO RS232 CONVERTER CABLE	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A
CAGE CODE 43321		DWG. NO. USB2.0-RS232	REV. A
SCALE: NONE		CAD FILE: USB2.0-RS232.SLDRW	SHEET 1 OF 1