


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/25/2019	GUTTADAURO
B	ECN 10616 EDIT TEXT	08/07/2020	GUTTADAURO



ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR
 TWO 22AWG CONDUCTORS STRANDED TINNED COPPER CONDUCTORS
 OVERALL ALUMINIZED POLYESTER SHIELD WITH STRANDED TINNED COPPER DRAIN WIRE PLUS TINNED COPPER BRAIDED SHIELD.
 JACKET: LSZH, BLACK
 CABLE UL VW-1 RATED



MIGHTY MOUSE
 801-009-01NF6-4SA
 JACK CONNECTOR, 4 SOCKET CONTACTS
 ALUMINUM/CADMIUM FINISH W/ OLIVE DRAB CHROMATE

USB SERIES "A" PLUG
 MOLDED HOOD
 LSZH



MODEL NUMBER	LENGTH FEET [METER]
USB228-MFZ-1F	1 [.98]
USB228-MFZ-10F	10 [1.64]

- NOTES:
- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 - TEST ASSEMBLY FOR SHORTS, CONTINUITY, AND INSULATION RESISTANCE 200 MEGAOHMS MIN.
 - CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 - LABEL SHALL BE PLACED ON CABLE WITH P/N AND DATE CODE.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BPUCHASKI	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	CHECKED BY DFRISIELLO	11/25/2019	CATEGORY USB
	APPROVED BY GUTTADAURO	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION USB 2.0 MM-F AM 901 AL/CD OLIVE LSZH W/DC
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	CAGE CODE 43321	DWG. NO. USB228-MFZ
		SCALE: NONE	CAD FILE: USB228-MFZ.SLDDRW
			REV. B