

Specifications

Mechanical Specifications

Enclosure	Dark Gray ABS
Ground Clamp	10 AWG Max.
Cable Dia. Range	0.394" to 0.551" (10 to 14 mm)
Operating Temperature	-40 C (-40 F) to +80 C (+176 F)
Weight	.38 lb. (.17 kg)
Dimensions	6.3 x 3.15 x 2.17 (inches) 160 x 80 x 55 (mm)
RoHS Compliant	Yes

Electrical Specifications

Connectors	(2) Removable Terminal Strips
CAT6 Data Lines	Pair 1: Pins 1/2, Terminal Strip Pair 2: Pins 3/4, Terminal Strip Pair 3: Pins 5/6, Terminal Strip Pair 4: Pins 7/8, Terminal Strip
PoE Clamping Voltage	58 Volts
Data Line Impedance	100 Ohms Balanced

