

Specifications

Electrical	
Impedance	50 Ohms
Frequency Range	DC ~ 11 GHz
Voltage Rating	1500 Volts Peak
Dielectric Withstanding Voltage	2500 Volts RMS
Insertion Loss	.15 dB Max.
Mechanical	
Mating	NMO/TAD Threaded Coupling 5/8-24-UNEF Threaded Coupling
Mating Torque	15 inch pounds (170 N.cm) Max.
Material	
Body	Brass
Contact	Gold Plated Brass
Insulator	TFE
Environmental	
Temperature Range	-55C(-67F) to +85C(+185F)
Temperature Cycling	MIL-Std. 202
Weatherproof	Yes
Moisture Resistance	MIL-Std. 202
Corrosion	MIL-Std. 202
Vibration	MIL-Std. 202
Altitude	MIL-Std. 202
RoHS Compliant	Yes