

Premium Molded D-Sub Cable, DB25 Male / Female, 2.5 ft



CS2N25MF-2.5

Configuration

Connector 1	25-Pin D-Subminiature Male
Connector 2	25-Pin D-Subminiature Female
Connector 2 Specification	D-Sub

Mechanical Specifications

Cable Assembly

Temperature

Temperature Operating Range, deg C	0 to +80
Temperature Storage Range, deg C	0 to +40

Size

Length, in [mm]	30 [762]
Cable Color	Gray

Cable

Jacket Material	PVC
-----------------	-----

Connector 1

Type	25-Pin D-Subminiature Male
Configuration	Straight

Connector 2

Type	25-Pin D-Subminiature Female
Configuration	Straight

Plotted and Other Data

Notes:

- Values at +20 °C, sea level

Premium Molded D-Sub Cable, DB25 Male / Female, 2.5 ft from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/d-sub-premium-molded-d-sub-cable-db25-male-female-25-ft>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

CS2N25MF-2.5 CAD Drawing
Premium Molded D-Sub Cable, DB25 Male / Female, 2.5 ft

