


Specifications

Zin / Zout	50 ohm Nominal
Pass Band	Low: 900-2500 MHz Nominal High: 4900-5875 MHz Nominal
Insertion Loss	Typ. 0.75 dB (900-2500 MHz) Typ. 1.0 dB (4900-5850 MHz)
Ripple	Low: 0.75 dB max (900-2500 MHz) High: 0.75 dB max (4900-5850 MHz)
VSWR	Low: 2.0 max (900-2500MHz) High: 2.5 max (4900-5850 MHz)
Power Rating	1 Watt
Temperature Range	-40° C to +85° C
Dimensions (L x D x H)	4.6 x 2.6 x 1.7 (inches) 117 x 66 x 43 (mm)
Weight	0.55 lbs. (.25 kg)

Insertion Loss, Return Loss - Input to Low Port



Insertion Loss, Return Loss - Input to High Port

