


# Fiber Optic Patch Cable, Simplex SC UPC to ST UPC, SM OS2, 2.0mm LSZH, Yellow-10M



## FCA-1S2SCUSTUZ2-10

### Features

- Single Mode OS2 fiber optic cable assembly
- Simplex SC UPC to ST UPC
- Indoor Low smoke zero halogen (LSZH) cable
- Suitable for confined installations where flame resistance is required
- Custom lengths available with the same fast delivery

### Applications

- Telecom & Networking
- Data Centers
- Enterprise and Corporate Networks
- Broadcasting & Media Production
- Military & Defense
- Healthcare & Medical Imaging
- Transportation & Rail
- Oil & Gas

### Description

The FCA-1S2SCUSTUZ2-10 from L-com is a fiber optic patch cable that is equipped with simplex SC/UPC to ST/UPC connectors. This cable comes with a single mode OS2 fiber that offers stable, high-speed transmission over long distances. Our yellow fiber optic cable assembly has an LSZH-rated PE jacket.

This 10-meter-long simplex fiber optic cable has a fiber diameter of 9/125  $\mu\text{m}$  and a cable diameter of 2 mm. With an operating temperature range of -20 to 70 degrees C, this cable provides reliable performance across diverse conditions. Our patch cable assembly is suitable for applications such as telecom and networking, data centers, enterprise and corporate networks, broadcasting and media production, military and defense, healthcare and medical imaging, transportation and rail, and oil and gas.

Our fiber optic cable assembly can be customized in different lengths to fit specific installation needs, ensuring efficient network management in high-density setups without compromising delivery time or quality. L-com's FCA-1S2SCUSTUZ2-10 patch cable has a maximum insertion loss of 0.3 dB. Additional dimensions, specifications, and CAD drawings for this simplex fiber optic cable can be found on its downloadable PDF datasheet.

L-com has one of the largest in-stock selections of single mode OS2 fiber optic cable assemblies for international and domestic orders. We are committed to delivering excellent service to support our customers in maintaining the continuity and reliability of their networks. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal simplex SC/UPC to ST/UPC patch cable that meets your requirements.

### Configuration

|                     |                     |
|---------------------|---------------------|
| Function            | Patch               |
| Cable Type          | Simplex Single Mode |
| Mode                | Single Mode         |
| Mode Class          | OS2                 |
| Fiber Diameter      | 9/125 $\mu\text{m}$ |
| Connection 1 Type   | SC                  |
| Connection 1 Polish | UPC                 |
| Connection 2 Type   | ST                  |
| Connection 2 Polish | UPC                 |
| Cable Color         | Yellow              |

### Optical Specifications

| Description                  | Minimum | Typical | Maximum | Units |
|------------------------------|---------|---------|---------|-------|
| Return Loss - LC, ST, SC, FC | 50      |         |         | dB    |

Fiber Optic Patch Cable, Simplex SC UPC to ST  
UPC, SM OS2, 2.0mm LSZH, Yellow-10M



## FCA-1S2SCUSTUZ2-10

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                     |
|----------------|---------------------|
| Length         | 10 m [393.70 in]    |
| Width/Diameter | 2 mm                |
| Weight         | 15.42 g [0.034 lbs] |

#### Cable

|                                            |       |
|--------------------------------------------|-------|
| Cable Type                                 | Patch |
| Static Bend Radius                         | 15 mm |
| Dynamic Bend Radius                        | 30 mm |
| Max Crush Resistance, Short Term (N/100mm) | 200   |
| Max Crush Resistance, Long Term (N/100mm)  | 50    |

### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | SC          | ST          |
| Connector Polish | UPC         | UPC         |

### Environmental Specifications

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Fiber Optic Patch Cable, Simplex SC UPC to ST  
UPC, SM OS2, 2.0mm LSZH, Yellow-10M



## FCA-1S2SCUSTUZ2-10

### Typical Performance Data

### How to Order

Part Number Configuration:

**FCA-1S2SCUSTUZ2**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: FCA-1S2SCUSTUZ2-12 = 12 meters long cable  
FCA-1S2SCUSTUZ2-10F = 10 feet long cable

Fiber Optic Patch Cable, Simplex SC UPC to ST UPC, SM OS2, 2.0mm LSZH, Yellow-10M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/fiber-optic-patch-cable-simplex-sc-upc-st-upc-sm-os2-2.0mm-lszh-yellow-10m-fca-1s2scustuz2-10-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

FCA-1S2SCUSTUZ2-10 CAD Drawing
Fiber Optic Patch Cable, Simplex SC UPC to ST UPC, SM OS2, 2.0mm LSZH, Yellow-10M

