


## 4-Fiber LC UPC to ST UPC, OM3 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-15M



### FCA-4M3LCUSTURK2-15

#### Features

- 4X LC UPC to 4X ST UPC
- Indoor multimode OM3
- Riser (OFNR) rated cable
- 4.5mm with tight-buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

The L-com FCA-4M3LCUSTURK2-15 is a fiber optic breakout cable assembly that is equipped with 4-fiber LC/UPC to ST/UPC connectors. This breakout cable assembly comes with a multimode OM3 fiber, which is optimized for VCSEL laser sources, making it ideal for 10Gb Ethernet up to 300 meters and 40G/100G Ethernet up to 100 meters, and offers a bandwidth of 2000 MHz·km, ensuring high-speed data transmission with minimal signal loss. The aqua blue fiber optic cable has an OFNR-rated PVC jacket and a length of 15 meters.

Our fiber optic breakout cable is a robust and versatile fiber optic assembly designed for high-performance data transmission in various environments. L-com's OM3 breakout fiber assembly guarantees outstanding network performance for enterprise networks, storage area networks (SANs), or high-speed backbones. With an operating temperature range of -20 to 70 degrees C, this cable assembly provides reliable performance across diverse conditions.

This fiber optic cable from L-com is suitable for applications such as data centers, passive optical networks (PON), local area networks (LAN), enterprise networking, storage and cloud based services, AI data storage and communications, headend termination to a fiber backbone, and terminations of data center fiber rack system. Our breakout cable comes with a cable diameter of 4.5 mm and has an insertion loss of 0.3 dB. Additional dimensions, specifications, and CAD drawings for this 4-fiber cable assembly can be found on its downloadable PDF datasheet.

L-com has one of the largest in-stock selections of LC/UPC to ST/UPC fiber optic breakout cords for international and domestic orders. We are committed to delivering excellent service to support our customers in maintaining the continuity and reliability of their networks. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal OM3 multimode fiber optic cable that meets your requirements.


#### Configuration

|                     |                  |
|---------------------|------------------|
| Function            | Breakout         |
| Cable Type          | Base-4 Multimode |
| Mode                | Multimode        |
| Mode Class          | OM3              |
| Fiber Diameter      | 50/125 µm        |
| Connection 1 Type   | LC               |
| Connection 1 Polish | UPC              |
| Connection 2 Type   | ST               |
| Connection 2 Polish | UPC              |
| Cable Color         | Aqua Blue        |

#### Optical Specifications

| Description                  | Minimum | Typical | Maximum | Units |
|------------------------------|---------|---------|---------|-------|
| Return Loss - LC, ST, SC, FC | 30      |         |         | dB    |

4-Fiber LC UPC to ST UPC, OM3 Multimode Distribution  
Cable, 4.5mm Riser, 2.0mm breakout, Aqua-15M



## FCA-4M3LCUSTURK2-15

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                      |
|----------------|----------------------|
| Length         | 15 m [590.55 in]     |
| Width/Diameter | 4.5 mm               |
| Weight         | 110.68 g [0.244 lbs] |

#### Cable

|                                            |          |
|--------------------------------------------|----------|
| Cable Type                                 | Breakout |
| Static Bend Radius                         | 34 mm    |
| Dynamic Bend Radius                        | 67 mm    |
| Max Crush Resistance, Short Term (N/100mm) | 1,000    |
| Max Crush Resistance, Long Term (N/100mm)  | 300      |

### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | LC          | ST          |
| Connector Polish | UPC         | UPC         |

### Environmental Specifications


|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

4-Fiber LC UPC to ST UPC, OM3 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-15M



## FCA-4M3LCUSTURK2-15

### Typical Performance Data

### How to Order

Part Number Configuration:

**FCA-4M3LCUSTURK2**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: FCA-4M3LCUSTURK2-12 = 12 meters long cable  
FCA-4M3LCUSTURK2-10F = 10 feet long cable

4-Fiber LC UPC to ST UPC, OM3 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-15M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/4-fiber-lc-upc-st-upc-om3-multimode-distribution-cable-4.5mm-riser-2.0mm-breakout-aqua-15m-fca-4m3l-custurk2-15-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

FCA-4M3LCUSTURK2-15 CAD Drawing

4-Fiber LC UPC to ST UPC, OM3 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-15M

