

# HyperLink Wireless Special Order - 2.4 GHz 5 dBi Mobile Omnidirectional Elevated Feed Antenna

#### **Applications and Features**

**Applications:** 

- 2.4 GHz ISM Band
- IEEE 802.11b and 802.11g Wireless LAN
- Bluetooth<sup>®</sup>
- WiFi
- Wireless Video Systems
- Multipoint and Mobile Applications

Features:

- Superior Performance
- Compact Size
- Built-in Shock Spring
- Indoor or Outdoor Use
- TAD/NMO mounting
- Fixed and Magnetic Mounts Available



# **Description**

#### **High Performance**

The HyperGain® HG2405UR-NMO is a high performance omnidirectional elevated feed antenna designed for the 2.4 GHz ISM band. This compact and lightweight antenna is ideally suited for IEEE 802.11b and 802.11g wireless LANs, public wireless hotspots, Bluetooth® and other multipoint and mobile applications where high gain and wide coverage is desired. This antenna features a co-linear stacked design with an elevated feed point. This allows the antenna to operate using a very small ground plane.



#### **Applications**

Measuring 14.5" long, this antenna features an aesthetic black finish. It features a built-in shock spring and is designed with a standard TAD/NMO Motorola-type connection that allows for ease of installation to similar TAD/NMO mounting systems.



Model: HG2405UR-NMO


## **Specifications**

## **Electrical Specifications**

Frequency Range	2400-2500 MHz	
Gain	5 dBi	
Impedance	50 Ohm	
VSWR	< 2.0:1 avg.	
Power Rating	200 Watts	

## **Mechanical Specifications**

Weight	0.36 lbs. (0.16 kg)	
Length	14.5" (368 mm)	
Finish	Black	
Mounting	TAD/NMO	
Polarization	Vertical	
Radiator	Stainless Steel	
Base	Powder Coated Brass	



#### **Available Mounts for this Antenna**

Brass	Permanent	NMO	Mounts



3/4 Inch Hole (19 mm)

For panels up to 5/32 Inch (4 mm) thick



3/8 Inch Hole (9.5 mm)

For panels up to 1/8 Inch (3.2 mm) thick



NMO Mobile Mount to N-Female Bulkhead Adapter

5/8 Inch Hole (16 mm), For panels up to 11/16 Inch (17 mm) thick



NMO Mobile Mount to Mini-UHF-Female Bulkhead Adapter

3/8 Inch Hole (9.5 mm Hole), for panels up to 11/16 Inch (17 mm) thick

#### **Magnetic NMO Mounts**



Chrome Magnetic NMO Mount w/Rubber Boot,

3 Inch Diameter Base (76.2 mm)