

2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail



## HG2471-06DPU-6RTP

### Features

- Reverse Polarity TNC (RP-TNC) Male Connector
- 6 x Vertical Polarization
- 6x6 MIMO Functionality
- Outdoor Rated Omnidirectional Antenna
- 2.4 GHz, 5 GHz, 6 GHz WiFi Bands
- 6 dBi gain

### Applications

- Infotainment systems, Routers, WiFi hotspots, HD video transmission, Gateways, Dash cameras, Public transportation
- WiFi 6e (802.11ax) networks
- Connected cars or self-driving cars, Fleet management, Logistics
- Public Safety Networks
- IoT, Industrial IoT, Zigbee, Bluetooth, WiFi

### Description

The HG2471-06DPU-6RTP WiFi 6e 6x6 MIMO Omni Antenna from L-com is a high performance omnidirectional antenna designed for the 2400 MHz to 7125 MHz bands and is available to ship same day. It features 6 (six) pigtails terminated with Reverse Polarity TNC (RP-TNC) Male connectors for 6x6 MIMO applications. It is a UV protected, outdoor rated antenna with omni-directional pattern. The HG2471-06DPU-6RTP is ideally suited for 802.11 protocols including 802.11ax as well as IoT, Zigbee and Bluetooth.

The L-com high performance omni HG2471-06DPU-6RTP is a rugged antenna providing broad coverage, low latency, increased network capacity and 6 dBi gain. This RP-TNC male omnidirectional antenna is suitable for commercial radios and access points in public and private networks that are equipped with RP-TNC female connectors. L-com's HG2471-06DPU-6RTP supports 2.4, 5 and 6 GHz bands.

This WiFi 6e HG2471-06DPU-6RTP omni antenna with 6 RP-TNC male connectors, as well as our wide selection of superior quality RF parts, ships same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

### Configuration

Design	Omni
Band Type	Dual
Radiation Pattern	Omni Directional
Polarization	Vertical
Cable Type	RG58/U
Connector Type	TNC Male Reverse Polarity

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2.4		7.25	GHz
Input VSWR			2:1	
Impedance		50		Ohms
Input Power			50	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail](#)

2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor  
Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail



## HG2471-06DPU-6RTP

### Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2,400-2,500	5,150-7,250				MHz
Bandwidth	100	2100				MHz
Gain	6	6				dBi
Horizontal HPBW	360	360				Degrees
Vertical HPBW	45	30				Degrees

### Mechanical Specifications

Radome Material	UV Resistant ABS
<b>Size</b>	
Length	7.1 in [180.34 mm]
Width	5.94 in [150.88 mm]
Height	5.94 in [150.88 mm]
Mounting Mast Diameter	1.57 to 1.96 in [39.88 to 49.78 mm]
Weight	3.52 lbs [1.6 kg]

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +70 deg C
Wind Survivability	124 MPH [199.56 KPH]
Humidity	5 to 95 %

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data


Notes:

2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor  
Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail

**HG2471-06DPU-6RTP**



**Radiation Patterns of 2450 MHz**




2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor  
Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail

**HG2471-06DPU-6RTP**



**Radiation Patterns of 5550 MHz**




2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail

**HG2471-06DPU-6RTP**



**Radiation Patterns of 6500 MHz**



2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2.4 GHz-2.5 GHz / 5.1 GHz-7.2 GHz, 6/6 dBi WiFi 6e 6x6 MIMO Outdoor Omni Antenna - 6 x RP-TNC Male Connector on 0.9 meter RG58 pigtail

L-com CAD Drawing

