

Wall Cabinets - Vertical Wall Enclosures



L-Com's low profile vertical wall mount rack enclosures are designed to securely mount your EIA-standard rack mount equipment and are made of heavy-duty steel. These enclosures feature locks on the front door and are ideal to mount anywhere floor space is limited. Available in 2U to 6U in both switch depth and server depth.

Model	LC-F2U400	LC-F2U400-WT	LC-F2U600-WT	LC-F2U700-WT	LC-F3U400	LC-F3U400-WT	LC-F3U550	LC-F3U550-WT	LC-F3U600-WT	LC-F3U700-WT
Description	2U Vertical Wall Mount, 400mm	2U Vertical Wall Mount, 400mm	2U Vertical Wall Mount, 600mm	2U Vertical Wall Mount, 700mm	3U Vertical Wall Mount, 400mm	3U Vertical Wall Mount, 400mm	3U Vertical Wall Mount, 500mm	3U Vertical Wall Mount, 500mm	3U Vertical Wall Mount, 600mm	3U Vertical Wall Mount, 700mm
RU	2U	2U	2U	2U	3U	3U	3U	3U	3U	3U
Upper Patch Panel Bracket	1U	1U	1U	1U	1U	1U	1U	1U	1U	1U
Adjustable Vertical Rail Mounting Depth Minimum to Maximum range (1in increments)										
Minimum	12.7in (325mm)	12.7in (325mm)	20.6in (525mm)	24.6in (625mm)	12.7in (325mm)	12.7in (325mm)	16.7in (425mm)	16.7in (425mm)	20.6in (525mm)	24.6in (625mm)
Maximum	15.7in (400mm)	15.7in (400mm)	23.6in (600mm)	27.5in (700mm)	15.7in (400mm)	15.7in (400mm)	19.6in (500mm)	19.6in (500mm)	23.6in (600mm)	27.5in (700mm)
External Dimensions	L	22.96	22.96	30.8	34.8	22.96	22.96	28.7	32.96	34.8
	W	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3
	H	4.46	4.46	4.46	4.46	6.21	6.21	6.21	6.21	6.21
Weight Capacity	132 lbs									
Material	Cold rolled Steel									
Painting/Coating	Black Powder Coating	White Powder Coating	White Powder Coating	White Powder Coating	Black Powder Coating	White Powder Coating	Black Powder Coating	White Powder Coating	White Powder Coating	White Powder Coating
Rail Type	M6 and 12-24									
Equipment Mounting Hardware (included)	4 x M6 Wall Anchor Bolts; 12 x M6 Screws; 12 x 12-24 Screws									
Assembly	Assembled									
Compatibility and Standards	CE, PCI, NEMA Type-1 and IP20 protection, HIPAA, RoHS & REACH - please contact our customer service team at sales@l-com.com									
Shipping Weight	41.8	41.8	46.3	51.8	50.7	50.7	55.11	55.11	59.52	63.93

Model	LC-F4U400	LC-F4U400-WT	LC-F4U550-WT	LC-F4U600	LC-F4U600-WT	LC-F4U700-WT	LC-F4U900-WT
Description	4U Vertical Wall Mount, 400mm	4U Vertical Wall Mount, 400mm	4U Vertical Wall Mount, 500mm	4U Vertical Wall Mount, 600mm	4U Vertical Wall Mount, 600mm	4U Vertical Wall Mount, 700mm	4U Vertical Wall Mount, 900mm
RU	4U	4U	4U	4U	4U	4U	4U
Upper Patch Panel Bracket	1U	1U	1U	1U	1U	1U	1U
Adjustable Vertical Rail Mounting Depth Minimum to Maximum range (1in increments)							
Minimum	12.7in (325mm)	12.7in (325mm)	16.7in (425mm)	20.6in (525mm)	20.6in (525mm)	24.6in (625mm)	32.4in (825mm)
Maximum	15.7in (400mm)	15.7in (400mm)	19.6in (500mm)	23.6in (600mm)	23.6in (600mm)	27.5in (700mm)	35.4 (900mm)
External Dimensions	L	22.96	22.96	26.9	30.8	30.8	42.65
	W	25.3	25.3	25.3	25.3	25.3	25.3
	H	7.96	7.96	7.96	7.96	7.96	7.96
Weight Capacity	132 lbs						
Material	Cold rolled Steel						
Painting/Coating	Black Powder Coating	White Powder Coating	White Powder Coating	Black Powder Coating	White Powder Coating	White Powder Coating	White Powder Coating
Rail Type	M6 and 12-24						
Equipment Mounting Hardware (included)	4 x M6 Wall Anchor Bolts; 12 x M6 Screws; 12 x 12-24 Screws						
Assembly	Assembled						
Compatibility and Standards	CE, PCI, NEMA Type-1 and IP20 protection, HIPAA, RoHS & REACH - please contact our customer service team at sales@l-com.com						
Shipping Weight	48.5	48.5	54.01	57.32	57.32	61.72	71.7

Wall Cabinets - Vertical Wall Enclosures



L-Com's low profile vertical wall mount rack enclosures are designed to securely mount your EIA-standard rack mount equipment and are made of heavy-duty steel. These enclosures feature locks on the front door and are ideal to mount anywhere floor space is limited. Available in 2U to 6U in both switch depth and server depth.

Model	LC-F6U400	LC-F6U400-WT	LC-F6U550-WT	LC-F6U600	LC-F6U600-WT	LC-F6U700-WT	LC-F6U900	LC-F6U900-WT
Description	6U Vertical Wall Mount, 400mm	6U Vertical Wall Mount, 400mm	6U Vertical Wall Mount, 500mm	6U Vertical Wall Mount, 600mm	6U Vertical Wall Mount, 600mm	6U Vertical Wall Mount, 700mm	6U Vertical Wall Mount, 900mm	6U Vertical Wall Mount, 900mm
RU	6U	6U	6U	6U	6U	6U	6U	6U
Upper Patch Panel Bracket	2U	2U	2U	2U	2U	2U	2U	2U
Adjustable Vertical Rail Mounting Depth Minimum to Maximum range (1in increments)								
Minimum	12.7in (325mm)	12.7in (325mm)	16.7in (425mm)	20.6in (525mm)	20.6in (525mm)	24.6in (625mm)	32.4in (825mm)	32.4in (825mm)
Maximum	15.7in (400mm)	15.7in (400mm)	19.6in (500mm)	23.6in (600mm)	23.6in (600mm)	27.5in (700mm)	35.4 (900mm)	35.4 (900mm)
External Dimensions	L	26.9	26.9	26.9	30.8	30.8	34.7	42.6
	W	25.5	25.5	25.5	25.5	25.5	25.5	25.5
	H	11.5	11.5	11.5	11.5	11.5	11.5	11.5
Weight Capacity	132lbs							
Material	Cold rolled Steel							
Painting/Coating	Black Powder Coating	White Powder Coating	White Powder Coating	Black Powder Coating	White Powder Coating	White Powder Coating	Black Powder Coating	White Powder Coating
Rail Type	M6 and 12-24							
Equipment Mounting Hardware (included)	4 x M6 Wall Anchor Bolts; 12 x M6 Screws; 12 x 12-24 Screws							
Assembly	Assembled							
Compatibility and Standards	CE, PCI, NEMA Type-1 and IP20 protection, HIPAA, RoHS & REACH - please contact our customer service team at sales@l-com.com							
Shipping Weight	57.3	57.3	61.7	66.13	66.13	70.5	81.6	81.6