


MPO w/ pins to ST Fan-out, 24 fiber round, OM5 50/125µm  
Multimode, OFNR Jacket, Lime Green, 1 meter



## MPM24OM5-STR-1

### Features

- Fan-out connectors unclipped for custom Polarity requirements
- MPO fan-out to ST connectors for server-to-switch and other link aggregation
- OFNR (Riser Rated) Jacket complies with strict building codes
- Used to connect equipment that utilizes MPO style connectors and OM5 50/125µm Multimode cabling for aggregation of links

### Applications

- Link Aggregation
- Data Centers/Enterprise Networking
- Ethernet
- Server connectivity

### Description

The MPM24OM5-STR-1 from L-com is a fan-out cable assembly that comes with a MPO (w/ pins) male to ST male connector configuration. This fiber optic cable with 24 fibers features an OFNR-rated jacket and has a cable diameter of 3.8 mm. Our fan-out cable is suitable for applications such as data centers, Ethernet, link aggregation, and server connectivity. This lime green fiber optic cable assembly is available in a length of 1 meter and can withstand temperatures ranging from -40 to 75 degrees C.

Our MPO (w/ pins) to ST cable comes with a multimode OM5 fiber and has a fiber diameter of 50/125 µm. L-com's fan-out cable assembly is ideal for making connections within rack mounted or wall mounted fiber enclosures. Our fiber optic cable assembly can be customized in different lengths to fit specific installation needs, ensuring efficient network management in high-density setups without compromising delivery time or quality. Additional dimensions, specifications, and CAD drawings for this MPM24OM5-STR-1 fan-out cable can be found on its downloadable PDF datasheet.

L-com has one of the largest in-stock selections of fiber optic cable assemblies for international and domestic orders. Make your online purchase right now to take advantage of our same-business-day shipping. We are committed to delivering excellent service to support our customers in maintaining the continuity and reliability of their networks. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal multimode OM5 fan-out cable for your requirements.


### Configuration

|                     |                   |
|---------------------|-------------------|
| Function            | Fan-out           |
| Cable Type          | Base-24 Multimode |
| Mode                | Multimode         |
| Mode Class          | OM5               |
| Fiber Diameter      | 50/125 µm         |
| Connection 1 Type   | MPO (w/ pins)     |
| Connection 1 Gender | Male              |
| Connection 1 Polish | UPC               |
| Connection 2 Type   | ST                |
| Connection 2 Polish | PC                |
| Cable Color         | Lime Green        |

### Optical Specifications

| Description                  | Minimum | Typical | Maximum | Units |
|------------------------------|---------|---------|---------|-------|
| Return Loss - MPO            | 20      |         |         | dB    |
| Insertion Loss - MPO         |         |         | 0.75    | dB    |
| Return Loss - LC, ST, SC, FC | 20      |         |         | dB    |

MPO w/ pins to ST Fan-out, 24 fiber round, OM5 50/125µm Multimode, OFNR Jacket, Lime Green, 1 meter



## MPM24OM5-STR-1

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                |
|----------------|----------------|
| Length         | 1 m [39.37 in] |
| Width/Diameter | 3.8 mm         |

#### Cable

|  |         |
|--|---------|
| Cable Type                                 | Fan-out |
| Polarity                                   | Neutral |
| Breakout Diameter                          | 2 mm    |
| Static Bend Radius                         | 38 mm   |
| Dynamic Bend Radius                        | 76 mm   |
| Max Crush Resistance, Short Term (N/100mm) | 500     |
| Max Crush Resistance, Long Term (N/100mm)  | 100     |

### Connectors

| Description      | Connector 1        | Connector 2 |
|------------------|--------------------|-------------|
| Type             | MPO (w/ pins) Male | ST          |
| Configuration    | Straight           |             |
| Connector Polish | UPC                | PC          |

### Environmental Specifications


|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -40 to +75 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

MPO w/ pins to ST Fan-out, 24 fiber round, OM5 50/125µm Multimode, OFNR Jacket, Lime Green, 1 meter



## MPM24OM5-STR-1

### Typical Performance Data

### How to Order

Part Number Configuration:

**MPM24OM5-STR**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: MPM24OM5-STR-12 = 12 meters long cable  
MPM24OM5-STR-10F = 10 feet long cable

MPO w/ pins to ST Fan-out, 24 fiber round, OM5 50/125µm Multimode, OFNR Jacket, Lime Green, 1 meter from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/fiber-optic-mpo-w-pins-to-st-fan-out-24-fiber-round-om5-50-125um-multimode-ofnr-jacket-lime-green-1-meter>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# MPM24OM5-STR-1 CAD Drawing

MPO w/ pins to ST Fan-out, 24 fiber round, OM5 50/125µm Multimode, OFNR Jacket, Lime Green, 1 meter

