Category 5E UTP 24 AWG 4-Pair Stranded Conductor Orange, 1KFT

TC2594

Configuration

Jacket/Flame Rating	CMR

Electrical Specifications

Frequency	350 MHz to 1 MHz
Operating Voltage/Working Voltage (DC)	1,500 Vrms
Impedance	100 Ohms

Mechanical Specifications

Cable Assembly

Cable Type	Cat5e
Cable Flex	Standard
Cable Shield Layer Material	(UTP)

Temperature

Temperature Operating Range, deg C	-20 to +75

Size

Length, ft []	1,000 []
Weight, lbs/ft [Kg/m]	1,000 [1,488.16]
Cable Color	Orange
Jacket Diameter	0.215 in [5.46 mm]
Cable Jacket Thickness	0.026 in [0.66 mm]
One Time Minimum Bend Radius, in [mm]	1 [25.4]
Wire/Conductor Insulation Diameter, Nominal	0.038 in [0.97 mm]
Twisted Pair Insulation Diameter, Nominal	0.038 in [0.97 mm]
Max Continuous Length	1,000
Twisted Pair Insulation Thickness	0.007 in [0.18 mm]

Cable

Jacket Material	PVC
Wire/Conductor Construction	24 AWG, 7/32
Wire/Conductor Insulation Material	PE
Wire/Conductor Material and Plating	Copper
Twisted Pair Construction	24 AWG, 7/32
Twisted Pairl Insulation Material	Polyethylene
Number of Wire/Conductors	8
Number of Twisted Pairs	4

Plotted and Other Data

Notes:

- Values at +20 °C, sea level

© 2026 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

Category 5E UTP 24 AWG 4-Pair Stranded Conductor Orange, 1KFT

TC2594

Category 5E UTP 24 AWG 4-Pair Stranded Conductor Orange, 1KFT from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: https://www.l-com.com/ethernet-category-5e-utp-24-awg-4-pair-stranded-conductor-orange-1kft

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

© 2026 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

TC2594 CAD Drawing

Category 5E UTP 24 AWG 4-Pair Stranded Conductor Orange, 1KFT

© 2025 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.