



OWNER'S MANUAL:

1U Vented 4-Post Adjustable Shelf




Hardware Included
• M6 Screws (x8) • M6 Cage Nuts (x8) • M6 Plastic Washers (x8)
Maximum Weight Capacity: 45kg/99lb


1. SQUARED MOLE MOUNTING




Owner's Manual | **1U Vented 4-Post Adjustable Shelf**



- Locate the numbered square openings in the mounting rails where you plan to install your shelf. You will install cage nuts (included) into the square openings to provide an attachment point for the mounting screws (included)
 - o From the inside of the mounting rail, insert one of the flanges of the cage nut through the square opening. Press it against the side of the square opening. Each flange should engage one side of the square opening, not the top or bottom.
 - o Compress the cage nut at the sides slightly to allow the remaining flange to fit through the square opening. When the cage nut is properly installed, both flanges will protrude through the square opening and will be visible on the outer surface of the mounting rail.
- Slide the shelf in the rack/cabinet by angling the sliding shelf by nearly 30 degrees.
 - o You will need roughly 6U of space to install the shelf




Fit mounting rack rails within the slots



DETAIL A
SCALE 1 : 2

- (Referencing Detail, A) Align/fit the mounting rack rails within the slots for all four corners on the sliding shelf.
- Rotate to lower and mount the shelf to the front and rear rails of the rack/cabinet using the included mounting hardware.



- Use the included mounting screws and plastic washers to secure your shelf to the rack rail.