


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	06/01/2023	KGLEBOVA	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = $+1$ [25] / -0 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0 > 300 [7620] = $+5\%$ / -0 </p> <p>ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] FRACTIONS $.XX = \pm .02$ [5] $\pm 1/32$ $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$ </p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p>L-COM an INFINITI brand</p>	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	DRAWN BY KGLEBOVA	05/08/2023		
<p>CHECKED BY KLEITLEIN</p>	CHECKED BY KLEITLEIN	05/22/2023	<p>CATEGORY</p>	<p>COAXIAL</p>
	APPROVED BY AGANWANI	06/01/2023		
<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>	<p>PRODUCT DESCRIPTION</p> <p>BNC FEMALE TO MCX PLUG RIGHT ANGLE CABLE USING RG174 COAX , LF SOLDER</p>		<p>SIZE A</p>	<p>CAGE CODE 43321</p>
	COLOR VARIATIONS MAY OCCUR			
	SCALE: NONE	CAD FILE: LCCA31166.SLDDRW	REV. A	SHEET 1 OF 1