


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/08/2023	BPUCHASKI	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5\%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2$ [5]
 $.XX = \pm .02$ [5]
 $.XXX = \pm .005$ [1.3]

FRACTIONS
 $\pm 1/32$
 ANGLES $\pm 1^\circ$

THIRD-ANGLE PROJECTION

COLOR VARIATIONS
MAY OCCUR

APPROVALS

DATE

DRAWN BY

BPUCHASKI

05/08/2023

CHECKED BY

KLEITLEIN

05/08/2023

APPROVED BY

AGANWANI

05/08/2023

L-COMTM
an INFINIT[®] brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

COAXIAL

PRODUCT DESCRIPTION
**MCX Jack to MCX Plug Right Angle Cable
Using RG316 Coax with HeatShrink, LF Solder**

SIZE A CAGE CODE 43321 ITEM NO. LCCA31274 REV. A
SCALE: NONE CAD FILE: LCCA31274.SLDDRW SHEET 1 OF 1