


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/08/2023	BPUCHASKI	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 $\leq 12 [305] = +1 [25] / -0$
 $> 12 [305] \leq 60 [1524] = +2 [51] / -0$
 $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$
 $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$
 $> 300 [7620] = +5\% / -0$

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2 [5]$ FRACTIONS
 $.XX = \pm .02 [5]$ $\pm 1/32$
 $.XXX = \pm .005 [1.3]$ ANGLES $\pm 1^\circ$

THIRD-ANGLE PROJECTION

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

COLOR VARIATIONS
MAY OCCUR

APPROVALS
DRAWN BY
BPUCHASKI
05/08/2023
CHECKED BY
KLEITLEIN
05/08/2023
APPROVED BY
AGANWANI
05/08/2023

CATEGORY

COAXIAL

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

PRODUCT DESCRIPTION
SMA Male Right Angle to SMA Female Bulkhead
Cable Using RG316 Coax, RoHS

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	LCCA31302	A
SCALE: NONE	CAD FILE: LCCA31302.SLDDRW	SHEET 1 OF 1	