


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/18/2023	PSRINIVAS	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] = +1 [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] = +2 [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] = +4 [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] = +6 [152] / -0  
 $> 300$  [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
 $.X = \pm .2$  [5]      FRACTIONS  
 $.XX = \pm .02$  [5]       $\pm 1/32$   
 $.XXX = \pm .005$  [.13]      ANGLES  $\pm 1^\circ$

THIRD-ANGLE PROJECTION



APPROVALS

DATE

DRAWN BY

PSRINIVAS

5/10/2023

CHECKED BY

DFRISIELLO

05/10/2023

APPROVED BY

AGANWANI

05/18/2023

**L-COM**<sup>TM</sup>  
an INFINIT<sup>®</sup> brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

COAXIAL

PRODUCT DESCRIPTION

BNC Male Right Angle to BNC Male Right Angle  
Cable Using RG316-DS Coax, LF Solder, RoHS

SIZE

A

CAGE CODE

43321

ITEM NO.

LCCA31386

REV.

A

SCALE: NONE

CAD FILE: LCCA31386.SLDDRW

SHEET 1 OF 1