	6		5		4		3		2		1		
[1		1				1	REVISION	I			
F	DESCRIPTION	MATERIAL	FINISH				ZONE REV	DE	ESCRIPTION	DATE	CHANGED BY	APPROVED	
	BODY	BRASS	NICKEL			l	D2 D	UPDATE	D PER ECO-12549	02/01/2024	HBAKKE	AGANWANI	
	CONTACT	BRASS	GOLD									F	
	INSULATOR	PTFE											
	FERRULE	BRASS	NICKEL										
		RUBBER											
	RETAINING RING	BRASS	NICKEL										
	SHELL	BRASS	NICKEL										
	ONLEE	Brittee	HIGHLE										
Е		.31		 	.66								E
	-	— [8.0] —	-		[16.7]								
		HEX											
					()								
									F — -				
								-F	=				
Р													_
D						J							D
		\checkmark			٦/								
	-								40			-	
			· /			.03			<u>.40</u> [10.2]	-			
		.12	28	\mathcal{I}		[[1.0)]			.08			
С	[3.25] $($ $)$ $($											С	
		Т		_1		F							
	NOTES:		FERRULE	CRIMP SIZE	PIN CRIMP	SIZE	L	/					
	ELECTRICAL: IMPEDANCE: 50 OHMS	`								-			
	DIELECTRIC WITHSTAN	ND VOLTAGE	E: 1000 VOLTS	S RMS					ECOMMENDED				
	VOLTAGE RATING: 500 FREQUENCY RANGE:	VOLTS PEA	K					CA	ABLE STRIPPING				
В	CABLE RETENTION: > 4	45 POUNDS											В
	MISCELLANEOUS:												
	COMPONENTS SHALL	BE INDIVIDU	ALLY PACKAC	SED IN			OTHERWISE SPECIFIEI	D					
	ACCORDANCE WITH L-	-COM SPECI	FICATION PS-	0031.		DIMENSIO	TOLERANCES:	ERS	L =COr			$\cdot \leftarrow$	
	ALL DIMENSIONS ARE	FOR REFER	ENCE ONLY.			.X = . ± = XX.	2 [5] FRACTION 02 [0.5] ± 1/32		an INFINIT@	brand		L DIMENSIONS AND S PER ASME Y14.5	
	APPLICATION: WBC/LM	.XXX = ±.0	05 [0.13] ANGLES ±	: 1°	Website: www.L-com.	com	SCALE	SHEET					
А	REGULATORY COMPLI	>12 [30	≤12 [305] = +1 [25] / - ≤12 [505] = +2 [51] / -	-0 -0 -0 DESCRIPTIO	Phone: 1.800.341.5266 1.978.682.6936 NONE 1 OF 1 DESCRIPTION				А				
~	EU RoHS DIRECTIVI	>60 [1524] >120 [3048]	$ \begin{array}{l} \leq 12 \; [305] = +1 \; [25] \; / \; , \\ \leq 60 \; [1524] = +2 \; [51] \; / \; , \\ \leq 120 \; [3048] = +4 \; [102] \; / \\ \leq 300 \; [7620] = +6 \; [152] \; / \\ > 300 \; [7620] = +5\% \; / \; -0 \end{array} $	/ -0 / -0	CON, RP-SMA PLUG CRIMP LMR-100				~				
	THE INFORMATION CONTAINED IN THIS DRAW	ALL DIMENSIO	NS ARE FOR REFERENCE										
	EXPORTED FROM THE UNITED STATES IN ACC PROHIBITED.					UN-DIMENSIO MAY VA	NED/NON-CRITICAL FEATURY IN SIZE AND LOCATION	TURES SIZE C	43321 DFRISIELLO		ARSP-110	D D	
	LC LG Rev-D5 Asize 6		5		4		3		2	<u>/</u>	1	I	J
		I		I				I		I			