	8	7		6		5	*	1	3			2		1	
THE	INFORMATION CONTAINED IN DPERTY OF L-COM, INC. ANY REPI HOUT THE WRITTEN PERMISSION O	THIS DRAWING IS THE							REV			REVISIO	SNC	DATE	APPROVED
WIT	HOUT THE WRITTEN PERMISSION O	L-COM, INC. IS PROF	IBITED.							RE-MODELED				4/28/11	D.FRISIELLO
D	DESCRIPTION	MATERIAL	FINI	SH											
	BODY	BRASS	NICKEL	PLATE											
	DIELECTRIC	TFE	-												
	CENTER PIN	BRASS	GOLD	PLATE											
	GASKET	RUBBER	-												
	RETAINING RING	BRASS	NICKEL												
	SHELL	BRASS	NICKEL	PLATE											
C		φ. [14	.63 0]		-	-	1.11 [28.1] 73 [18.5								
-			.3 [8]	¥ 815 .00] IEX											
В	sma pli	JG				5/8	3-24 UNEF-2A				ΤΥ	PE N JAC	СК		
_	NOTES:														
	ELECTRICAL:						Ro	HS Co	mpliant	t 🗸					
	IMPEDANCE: 50 OH	MS								-					
	FREQUENCY RANG	500 VOLTS PFA	К				UNLESS OTHERW		APPROVALS	DATE			Global r		
	DIELECTRIC WITHSTA	NDING VOLTA	AGE: 1000	VOLTS RMS			DIMENSIONS ARE I		0	06/05/2001	-9		Connect		NDOVER, MA 01845
A							OVERALL CABLE LEN <12 [305] = + >12 [305] <60 [152 >60 [1524] <120 [304 >120 [3048] <300 [76 >300 [7620] =	1 [25] / -0 4] = +2 [51] / -0	CHECKED BY	06/05/2001	CATEGORY				
	MISCELLANEOUS:						>60 [1524] ≤120 [304 >120 [3048] ≤300 [76	8] = +4 [102] / -0 20] = +6 [152] / -0	APPROVED BY ENG	07/02/2001			COAXIA	L	
	COMPONENT SHAL						>300 [7620] = ALL OTHER DIMENSIO		I	F	PRODUCT DE	SCRIPTION			
	ACCORDANCE WIT						± = X. ± = XX.	.2 .02	CONFIGURATION UNDIMENSIONED MAY VAR	DETAILS OF FEATURES		TER SM			
	ALL DIMENSIONS AF			v			.XXX =	.005							REV
						COLOR VARIATIONS MAY OCCUR		SIZE A 43321 DWG. NO.		BA25	E				
							\square		REF		SCALE: NC		E: BA25.SLDDRV		SHEET 1 OF
			-			5	4		1		1				