



В

А

MATERIAL:

BODY BRASS CENTER CONTACTS: BRASS TEFLON INSULATORS

FINISH:

BODY: NICKEL PLATED CENTER CONTACTS: GOLD PLATED

45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 **RoHS Compliant** ~ L-com CONNECTIVITY PRODUCTS DATE APPROVALS UNLESS OTHERWISE SPECIFIED, DRAWN BY CATEGORY А DIMENSIONS ARE IN INCHES [mm MCCORMICK 08/16/01 COAXIAL TOLERANCES TO BE: ANGLES ±2° CHECKED BY .X ±.1 [2.5] .XX ±.01 [.25] .XXX ±.005 [.13] PRODUCT DESCRIPTION ENG 08/16/01 APPROVED BY BNC JACK TO SMA JACK OVERALL CABLE LENGTH TOL: D.PARHAM 08/16/01 ≤ 60 [1524] +3 [76.2] / - 0 > 60 [1524] +5% / -0% CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY FSCM NO. DWG. NO. SIZE REV. PROJ 43321 A BA588 C SCALE: NONE CAD FILE: BA588.SLDDRW SHEET 1 OF 1 5 3 2 1 4

B

8

6

7