REVISIONS						
	REV	DESCRIPTION	DATE	APPROVAL		
Ī	Α	TAKEN FROM DRAWNG 97-080401	08/11/09	DFP		
Ī						



## PREMIUM COAX ADAPTOR KIT

AN EXAMPLE OF A TYPICAL THREE ELEMENT COMBINATION IS SHOWN BELOW. ANY TWO CONNECTOR ELEMENTS IN A KIT MAY BE JOINED BY SCREWING THEM ONTO A COUPLER ELEMENT.







COUPLER



BNC PLUG

BAK400 CONSISTS OF 8 IDENTICAL COUPLER ELEMENTS AND 2 EACH OF THE FOLLOWING CONNECTOR ELEMENTS, A TOTAL OF 40 ELEMENTS.

<u>PLUGS</u>	<u>JACKS</u>
TYPE "N"	TYPE "N"
UHF	UHF
MINI UHF	MINI UHF
SMA	SMA
BNC	BNC
TNC	TNC
F	F
RCA PHONO	RCA PHONO

	APPROVALS	DATE			
UNLESS OTHERWISE SPECIFIED,	DRAWN BY	57112		Global 45 BEECHWOOD DRIVE	
DIMENSIONS ARE IN INCHES [mm]	D. PARHAM	08/10/2009	Connectivity NORIH ANDOVER, M		
OVERALL CABLE LENGTH TOLERANCE:	D. FRISIELLO	08/10/2009		01845	
\$12 [305] = +1 [25] / -0 >12 [305] \$60 [1524] = +2[51] / -0 >60 [1524] \$120 [3048] = +4 / -0	APPROVED BY	06/10/2009	CATEGORY		
>60 [1524] ≤120 [3048] = +4 / -0 >120 [3048] ≤300 [7620] = +6 / -0 >300 [7620] = +5% / -0%	D. CASTRO	08/11/2009		COAXIAL	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DI	ESCRIPTION	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005			KIT ADAPTOR 192 VARIOUS TYPES		
PROJECTION (+)	COLOR VARIATIONS MAY OCCUR		A 433	THE BITOLING.	
			SCALE: 1:1	CAD FILE: BAK400.SLDDRW SHEET 1 OF 1	