


LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-SMNMTXXX	WHERE XXX = LENGTH IN FEET	CA-SMNMT010 (10 FEET)
CA-SMNMTNXX	WHERE NXX = LENGTH IN INCHES	CA-SMNMTN16 (16 INCHES)
CA-SMNMTMXX	WHERE MXX = LENGTH IN METERS	CA-SMNMTM07 (7 METERS)
CA-SMNMTXMX	WHERE XMX = LENGTH IN DECIMEL METERS	CA-SMNMT3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
2. CABLE ASSEMBLY SHALL RECIEVE INSERTION LOSS TEST#TP-0027
3. CABLE ASSEMBLY SHALL WITHSTAND PULL TEST OF 40lbs WITHOUT ANY SEPERATION OR ELECTRICAL FAILURE
4. CABLE SHALL BE RoHS COMPLIANT
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031
6. CENTER PIN OF CONNECTORS TO BE SOLDERED OR CRIMPED ONTO CABLE INNER CONDUCTOR

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES <u>OVERALL CABLE LENGTH TOLERANCE</u> ≤ 12 [305] = +1 [25]/-0 >12 [305] ≤ 60 [1524] = +2 [51] /-0 >60 [1524] ≤ 120 [3048] = +4/-0 >120 [3048] U+2264300 [7620] = +6/-0 >300 [76290] = +5%/-0					SIZE	TITLE:				
					A	FABRICATION: CA-240 SERIES SMA MALE TO N-MALE ASSEMBLY with HEATSHRINK				
	B	HL_4177	08/11/09	Changed Length Reference Points To Outside Ends of Connectors						
	REV	ECN No.	DATE	DESCRIPTION	DRAWN BY	B.Puchaski	08/11/09	DRAWING No.	REV	
 Website: www.L-com.com Tel: 1-800-343-1455 Copyright © 2009 L-com, Inc. All rights reserved.				ORIGINATOR	B.Puchaski	05/27/09	F1063	B		
				APPROVAL	M. Audus	08/11/09	PART No.	CA-SMNMT [VAR.]		
				SCALE 1:1	SHEET 1/1	MATERIAL Noted	FILE No.	F1063-01		