


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

| REVISIONS | | | |
|-----------|---|--------|------------|
| REV | DESCRIPTION | DATE | APPROVED |
| B | ECN #3382, UPDATED DWG FORMAT, ADDED WIRING MAP, REVISED MODEL | 6/9/08 | E. STAUBLE |
| H | ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, ADDED NOTES & RoHS | 1/7/10 | D. CASTRO |
| J | ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION, ADDED LOGO NOTE | 6/9/10 | DFP |



| WIRING MAP | | | | | |
|------------|----------------|------|-------|---------------------|-------|
| "P1" | WIRE COLOR | "J1" | "P1" | WIRE COLOR | "J1" |
| 1 | BROWN | 1 | 20 | GRAY / GREEN | 20 |
| 2 | RED | 2 | 21 | GRAY / RED | 21 |
| 3 | ORANGE | 3 | 22 | GRAY / VIOLET | 22 |
| 4 | YELLOW | 4 | 23 | LIGHT GREEN / BLACK | 23 |
| 5 | GREEN | 5 | 24 | RED/BLACK | 24 |
| 6 | BLUE | 6 | 25 | ORANGE / BLACK | 25 |
| 7 | VIOLET | 7 | 26 | YELLOW / BLACK | 26 |
| 8 | GRAY | 8 | 27 | GREEN / BLACK | 27 |
| 9 | WHITE | 9 | 28 | LIGHT BLUE / BLACK | 28 |
| 10 | LIGHT GREEN | 10 | 29 | LIGHT BLUE / BROWN | 29 |
| 11 | BLACK | 11 | 30 | LIGHT BLUE / VIOLET | 30 |
| 12 | GRAY / BLACK | 12 | 31 | LIGHT BLUE / RED | 31 |
| 13 | BLUE / WHITE | 13 | 32 | LIGHT BLUE | 32 |
| 14 | VIOLET / WHITE | 14 | 33 | PINK | 33 |
| 15 | BROWN / WHITE | 15 | 34 | PINK / BLACK | 34 |
| 16 | BLACK / WHITE | 16 | 35 | PINK / GREEN | 35 |
| 17 | RED / WHITE | 17 | 36 | PINK / VIOLET | 36 |
| 18 | ORANGE / WHITE | 18 | 37 | PINK / RED | 37 |
| 19 | GREEN / WHITE | 19 | SHELL | DRAIN WIRE | SHELL |

| MODEL NUMBER | LENGTH | |
|--------------|--------|--------|
| | FEET | METERS |
| CS2N37MF-1 | 1.0 | 0.31 |
| CS2N37MF-2.5 | 2.5 | 0.76 |
| CS2N37MF-5 | 5.0 | 1.52 |
| CS2N37MF-10 | 10.0 | 3.05 |
| CS2N37MF-15 | 15.0 | 4.57 |
| CS2N37MF-25 | 25.0 | 7.62 |
| CS2N37MF-50 | 50.0 | 15.24 |

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

| | | | | |
|---|---|---------------------------------------|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 | APPROVALS DRAWN BY TJC CHECKED BY DFP APPROVED BY RC | DATE 9/28/01 9/28/01 10/3/01 | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | | CATEGORY D-SUBMINIATURE |
| | PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A FSCM NO. 43321 DWG. NO. CS2N37MF REV. J | PRODUCT DESCRIPTION CABLE, DB37M/F DBL SHLD |
| | SCALE: NONE | | CAD FILE: CS2N37MF.SLDDRW | SHEET 1 OF 1 |