THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT WRITTEN PERMISSION OF L-COM, INC IS PROHIBITED.

REVISIONS						
REV	DESCRIPTION	DATE	APPROVED			
D	ECN 1809 REVISED DESCRIPTIONS	07/20/04	MCCORMICK			
Е	ECN 1809 REVISED DESCRIPTIONS	06/11/07	J. KIEZULAS			
F	ECN 2993 CHANGE STEP TO GRADED	09/17/07	D.FRISIELLO			

TABLE						
PART NUMBER	FIBER COUNT	DIAMETER, MM [IN]	DESCRIPTION			
FOB625D6-M	6 COUNT	5.0 [.20]	62.5/125 micron Graded Index, Multi-mode			
FOB625D12-M	12 COUNT	6.0 [.24]	OFNP Rated Indoor/Outdoor Distribution			
FOB625D24-M	24 COUNT	7.0 [.28]	Cables.			
FOB500D6-M	6 COUNT	5.0 [.20]	50/125 micron Graded Index, Multi-mode			
FOB500D12-M	12 COUNT	6.0 [.24]	OFNP Rated Indoor/Outdoor Distribution			
FOB500D24-M	24 COUNT	7.0 [.28]	Cables.			
FOBSNGD6-M	6 COUNT	5.0 [.20]	9/125 micron Graded Index, Single-mode			
FOBSNGD12-M	12 COUNT	6.0 [.24]	OFNP Rated Indoor/Outdoor Distribution			
FOBSNGD24-M	24 COUNT	7.0 [.28]	Cables.			

## General Characteristics for Plenum (OFNP) Indoor/Outdoor Distribution Cables

Minimum Bend Radius: Under Installation Tensile Load: 15X outside diameter

Under Long-Term Tensile Load: 10X outside diameter

Operating Temperature: -40°C to +85°C Storage Temperature: -55°C to +85°C Crush Resistance: 1,800 N/cm Impact Resistance: 1,500 impacts Flex Resistance: 2,000 cycles

These specifications are subject to change without prior notification.

CABLE LENGTHS 50 METERS AND UNDER WILL BE SECURED WITH TWIST-TIE, PACKAGED INTO POLY BAG.

CABLE LENGTHS OVER 50 METERS WILL BE SPOOLED WITH 5' PIGTAILS.



45 Beechwood Drive North Andover, MA 01845

DRAWING TITLE

DRAWN BY	DATE		OUTLINE DRAWING	
MCCORMI	CK 12/17/01			
CHECKED B	Y DATE		DRAWING NUMBER	REV.
D.PARHAM	12/17/01	SIZE	FOB625D6-M	F
APPROVED	BY DATE	A	FILE NAME	SHEET
R.CARRICI	12/17/01		FOB625D6-M-OD1.DOC	1 OF 1