


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/19/2021	GUTTADAURO

## 3 IN 1 MODULAR CRIMPING TOOL



### SPECIFICATIONS:

#### \* Feature

1. All in one VDV (Voice/Data/Video) modular plug crimper combines with wire stripper and cutter.
2. Crimps 8P8C/RJ45, 6P6C/RJ12, 6P4C/RJ11, 4P4C & 4P2C modular plugs.
3. Strips/cuts round and flat cables, stripping length 1/2" and 1/4" are available for flat cable.

\* **Length** 7.5" (190 ± 3mm)

\* **Weight** 316g



\* **Finished** Black Oxide Finished And Hardened.

\* **Handle** Blue (PP)

\* **Replacement Blade** : HT-RB08S

### NOTE:

1. CRIMPING TOOL SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	08/19/2021	
APPROVED BY GUTTADAURO	08/19/2021	CATEGORY TELECOM/MODULAR	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION 3 IN 1 MODULAR CRIMP TOOL	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>HT-468R</b>
SCALE: NONE		CAD FILE: HT-468R.SLDDRW	
SHEET 1 OF 1			REV. <b>A</b>