

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REPLACES TDT-OD1	6/24/14	D. CASTRO



**SPECIFICATIONS:**

**DEVICE**  
D-SUB CONTACT INSERTION & EXTRACTION TOOL.

**MATERIAL**  
CONTACT: PHOSPHOR BRONZE, GOLD FLASH OVER NICKEL.  
INSULATOR: PBT w/ GLASS FIBER (UL 94V-0 RATED)  
BRACKET: ZINC ALLOY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY B.MAZEJKA	DATE 11/04/2003	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CHECKED BY C.McCORMICK	11/04/2003		CATEGORY TELECOM/MODULAR			
	APPROVED BY D.PARHAM	11/04/2003	PRODUCT DESCRIPTION ECONOMY INSERT & EXTRACT TOOL				
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. TDT</td> <td>REV. <b>A</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TDT
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TDT	REV. <b>A</b>				