



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/06/18	JLABOY



"P1"
2X, USB 3.0 PLUG
SERIES "C"
LEFT/RIGHT EXIT
30μ INCHES
GOLD PLATING



WIRE MAP					
"P1"	SIGNAL NAME	CONDUCTOR	"P2"	SIGNAL NAME	COLOR
A1,B1,A12,B12	GND	ALL DRAIN WIRES	A1,B1,A12,B12	GND	N/A
A4,B4,A9,B9	VBUS	INDV. (26AWG)	A4,B4,A9,B9	VBUS	RED
A5	CC	INDV. (32AWG)	A5	CC	BLUE
B5	VCONN	N/C	B5	VCONN	N/A
A6	Dp1	SHIELDED	A6	Dp1	GREEN
A7	Dn1	PAIR(34AWG)	A7	Dn1	WHITE
A2	SSTXp1	SHIELDED	B11	SSRXp1	YELLOW
A3	SSTXn1	PAIR(30AWG)	B10	SSRXn1	GREEN
B11	SSRXp1	SHIELDED	A2	SSTXp1	ORANGE
B10	SSRXn1	PAIR(30AWG)	A3	SSTXn1	BROWN
B2	SSTXp2	SHIELDED	A11	SSRXp2	BLACK
B3	SSTXn2	PAIR(30AWG)	A10	SSRXn2	BLUE
A11	SSRXp2	SHIELDED	B2	SSTXp2	WHITE
A10	SSRXn2	PAIR(30AWG)	B3	SSTXn2	RED
A8	SBU1	INDV. (32AWG)	B8	SBU2	BROWN
B8	SBU2	INDV. (32AWG)	A8	SBU1	ORANGE
SHELL	SHIELD	BRAID	SHELL	SHIELD	N/A

UL STYLE 2725,
(4) 30AWG SHIELDED STRANDED TINNED COPPER TWISTED PAIRS
(1) 34AWG SHIELDED STRANDED TINNED COPPER TWISTED PAIR
(4) 32AWG STRANDED TINNED COPPER CONDUCTORS
(1) 26AWG STRANDED TINNED COPPER CONDUCTOR
OVERALL ALUMINUM/POLYESTER SHIELD PLUS TINNED
COPPER BRAID SHIELD
JACKET: PVC, BLACK (NOM DIA. .189" [4.8])

PART NUMBER	LENGTH METERS [FEET]
U3A00079-03M	0.3 [.98]
U3A00079-05M	0.5 [1.64]
U3A00079-1M	1.0 [3.28]

- NOTES:**
- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - L-COM LOGO AND USB ICON MAY BE ON ANY SIDE OF THE OVERMOLD FOR USB SERIES "C" END.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845							
	DRAWN BY S.LI	12/07/17		CATEGORY	USB						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY B.ZHANG	12/07/17		PRODUCT DESCRIPTION							
	APPROVED BY S.PAN	12/07/17		CA, USB 3.0 TYPE C RA/TYP C RA							
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE</td> <td>FSCM NO.</td> <td>DWG. NO.</td> <td>REV.</td> </tr> <tr> <td>A</td> <td>43321</td> <td>U3A00079</td> <td>A</td> </tr> </table>	SIZE	FSCM NO.	DWG. NO.	REV.	A	43321	U3A00079	A
SIZE	FSCM NO.	DWG. NO.	REV.								
A	43321	U3A00079	A								
	SCALE: NONE	CAD FILE: U3A00079.SLDDRW	SHEET 1 OF 1								