


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/31/07	D.FRISIELLO
B	ECN 9549 REMOVED CENTER HOLE FROM PLATE AND RoHS	12/10/18	B.PUCHASKI



**NOTES:**

1. MATERIAL: .06 [1.5] THK COLD ROLLED STEEL.
2. FINISH: FLAT BLACK POWDER COAT.
3. KIT CONTAINS 4, #6-32 UNC SCREWS.
4. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY D.FRISIELLO	DATE 5/31/07		50 HIGH STREET NORTH ANDOVER, MA 01845	
	CHECKED BY P.MCNEIL	DATE 5/31/07		CATEGORY SUB PANELS	
	APPROVED BY P.MCNEIL	DATE 5/31/07	PRODUCT DESCRIPTION 2 D-HOLE SUB PANEL	SIZE <b>A</b>	FSCM NO. <b>43321</b>
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	DWG. NO. USP222B	REV. <b>B</b>